











EURACRYL

EQUIPMENT FOR TRANSPARENCY


-  2 ... 10 mm (... 25 optional)
-  no limit
-  0 ... 4 m/min (... 8 m/min optional)
-  0 ... 12.000 rpm
-  230/380 V - 50/60 Hz - 2,0 kW
-  240 kg
-  www.euracryl.com/v-slot



Bedienungsfeld - Control panel
Panel de control - Pannello di controllo
Tableau de commande



Führung - Guide - Guia - Guida - Guide



Präzisse Bearbeitung - Precise machining
Mecanizado preciso - Usinage précis
Lavorazione precisa



Einfacher Werkzeugwechsel - Easy tool change
Facil cambio de herramienta - Changement
d'outil facile - Facile cambio utensile

